

T 3425 991 U



Data Overview

Description:	Female Plug; Plastic; 6 Pin; Solder; Silver; 4-6mm; IP40
rated voltage	300 V
number of positions (w/o PE)	6
rated current (40 °C)	7 A
termination	solder pin
contact plating	silver
IP-class mated	IP40

Product Availability	Currently not on stock
Packing Unit:	50 Pieces
Min. Order Quantity:	50 Pieces

Price per Piece:	€2.97
Total Price plus VAT:	€148.50

[Send Request](#) ✉

[Add to Cart](#)

[Stock of our Distributors](#) ▾

Technical Data

General Characteristics	+
part category	female cable connector
gender	female
locking system	bayonet ring
housing style	straight
minimum cable diameter	4 MM
maximum cable diameter	6 MM
lower temperature	-40 GC
upper temperature	100 GC
IP-class mated	IP40
Electrical Characteristics	+
Further Characteristics	+
Downloads ↓	+

Frequently Asked Questions

- Which components belong to a complete bill of materials (BOM)? +
- Amphenol as a supplier of complete assemblies and plug & play solutions +
- What options are there for direct transfer to a printed circuit board? +
- How does the transmission of the cable shielding work with M16B connectors? +
- Crimping or soldering - what are pros & cons? +
- Tarnishing of silver-plated contacts - what's the reason? +
- What options are there for color adjustments to the application? +
- M16 receptacles with hex nut instead of ring nut? +
- What are the 5 and 7 pole stereo layouts used for? +
- What does the U at the end of the part number stand for? +

This might interest you



Disclaimer: No liability is accepted for the correctness and completeness of the suggested accessories.

- [Contact](#)
- [Downloads](#)
- [Imprint](#)
- [General Conditions](#)
- [Career](#)
- [Privacy Policy](#)
- [Privacy Settings](#)



Newsletter

I would like to receive the newsletter on the latest products, current trade fairs and promotions and give the following [consent](#).

[Subscribe to Newsletter](#)