



Catalog No. TC142

Description: SADDLE SUPPORT BASE .9X.5IN NAT NYL

UPC No 5414363058229

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 23.42mm (0.922 Inches), Width of 14.29mm (0.563 Inches), Height of 10.72mm (0.422 Inches), Mount with #10 Screw, Bulk Pack

Descriptors

Category	Cable tie mounts
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Application	Used for wire bundles, cables, and hoses to panels

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Mount Size	#10
------------	-----

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	23.42 mm
Length	0.92 inch
Width	14.29 mm
Width	0.563 inch

by ABB

ETIM	EC000449 Mounting base and -element for cable ties
Height	10.72 mm
Height	0.42 inch
Type of fastening	Other
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A