




MATERIALS:

Connector:

Body: Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper

Solder Turret Terminal Screws: Steel

Shielded Housing: Die cast aluminum Alloy A380 or A384.

Finish: Blue baked enamel per Federal Standard 595 #25109 over Phosphoric Etch.

Marking: "Pomona Electronics Calif."

Cover: 1.02 (.040) thick aluminum 1100-H14

Finish: Clear anodized.

Screws: Steel 4 ea. #2-32 x 1/4" Pan Head self-tapping

RATINGS:

Operating Voltage: Inner Conductor/Shield: 500 VRMS Max.

Operating Temperature: -55°C to +150°C

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 3239

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90169 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com