Precautions for use | General notes

ML-20 made in JAPAN

2021-12-07 Notice of partial product discontinuation. PDF

From February 1, 2022, only 14P, 16P and 18P products will be discontinued. Other products will continue to be sold.





Pitch 11mm | Relay

2021-12-07 Change of body material PDF

See other change notifications

E101073 | LR65928

Order model number

Order model number	ML-20-[Position]
Order example	ML-20-2P (An example of ordering with 2 positions.)

Basic information | Dimension | Optional | Download

Basic information

Rating	250V-20A
Insulation resistance	DC500V、100MΩ Min
Withstand voltage	AC2000V (1minute)
Certificates & Approvals	UL・CSA (Please specify CSA certified products when ordering)
Position	2～6、8、10、12、14、16、18
Main insulator	Phenolic (UL94V-0)
Insulator (Cover)	Polycarbonate (UL94V-0) Thickness 2P～5P : t=1.0mm / 6P～18P : t=1.5mm
Terminal screw	M4×8 Screw with square washer 、Torque 1.2N・m MAX
Body color	B (Black)
Installation	Screw
Note	1.When tightening the terminal screw without connecting the electric wire, tighten it with a torque of 0.2 to 0.3 Nm.

List of partial product change notifications

2021-12-07	Change of body material PDF
2013-10-03	Notice of partial product changes. PDF

Related products


ML-1



ML-1

Add to My List

ML-11-30F



ML-11-30F

Add to My List

ML-11-50F



ML-11-50F

Add to My List

COPYRIGHT © SATO PARTS CO.,LTD. ALL RIGHTS RESERVED.

Downloaded from Arrow.com.