

Part Number : [1301100021](#)

Product Description : Super-Safeway 100W 12V Halogen Floodlight, Magnet Mount, with Guard, For Use With Low-voltage Workstation, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')

Series Number : 130110

Status : Obsolete

Product Category : Lamps and Lights

Engineering Number : 8500M



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Lamps and Lights
Series	130110
Description	Super-Safeway 100W 12V Halogen Floodlight, Magnet Mount, with Guard, For Use With Low-voltage Workstation, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678885009

Electrical

Lamp Wattage - Maximum	100W
On/Off Switch	No
Voltage (Fixture) - Maximum	12V AC/DC

Physical

Bulb Type	Quartz Halogen
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	N/A
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	374.65mm (14.750")
Lamp Type	BRL
Length	279.40mm (11.000")
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stand
Outlet	None

Packaging Type	Carton
----------------	--------

This document was generated on Sep 04, 2025

Obsolete