

YAV14T3BOX, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14T3BOX](#)



Uninsulated Ring Terminal For 16 - 14 AWG

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	<ul style="list-style-type: none"> • 20 AWG • 18 AWG • 16 AWG • 14 AWG
Conductor - Copper Solid Size	<ul style="list-style-type: none"> • 20 • 18 AWG • 17 AWG • 16 AWG • 15 AWG • 14 AWG • 13 AWG • 12 AWG

Conductor - Copper Solid Size Range	20 AWG -12 AWG
Conductor - Copper Str Aircraft Size	<ul style="list-style-type: none"> • AN 20 • AN 18 • AN 16 • AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.16 in
Dimension - L Length Overall mm	25 mm
Dimension - Pad Width inch	0.44 in
Package Height	0.000 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	5/16 "
Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Z inch	0.32 in
Dimension - Bolt Size fraction	5/16
Dimension - Length Overall inch	0.99 in
Dimension - D inch	0.58 in
Dimension - N inch	0.25 in

General

Trade Name	HYLUG™
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard

Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810533604
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810533604

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YAV14T3BOX-SPEC-EN | REV 4/2026