

## Han3A RJ45 PFT adapter



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 515 0020
Specification	Han3A RJ45 PFT adapter
HARTING eCatalogue	<a href="https://b2b.harting.com/09455150020">https://b2b.harting.com/09455150020</a>

### Identification

Category	Connectors
Series	RJ45
Element	Adapter
Specification	for fixing of RJ45 jacks

### Version

Size	3 A
Shielding	Unshielded
PCB fixing	With snap-in clip

### Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	EN 45545-2
Approvals	DNV GL

## Commercial data

Packaging size	100
Net weight	3.04 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140060920
ETIM	EC002310
eCl@ss	27440210 Fixing element for industrial connectors