

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202480022

Status:

Active

Overview:

Brad Passive-Signal and Safety MPIS Boxes

Description:

MPIS Micro-Change (M12) Passive Junction Box, Top-Mount, 8 Ports, LED for PNP Sensor, WSOR Cable, 5.0m Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Passive Distribution Boxes
Series	120248
IP Rating	IP67
Overview	Brad Passive-Signal and Safety MPIS Boxes
Product Name	MPIS
UPC	889056140829
Physical	
Bus I/O	N/A
Cable Connector Orientation	Straight
Cable Length	5.0m
Home Run Cable Length	5.0m
Home Run Connector	N/A
Home Run Interface	Pigtail
Keyway	A-coded
LED Indicator	PNP Sensors
Material - Cable Jacket	TPU
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	808.852/g
Orientation	Top-Mount
Poles	4
Poles (wired)	4
Ports	4
Temperature Range - Operating	-25°C to +85°C
Wire/Cable Type	WSOR
Wiring Configuration	Single I/O per Port
Electrical	
Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC
Material Info	
Engineering Number	BTB800P-FBW-05
Reference - Drawing Numbers	
Sales Drawing	1202480019-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2021)10043-DC (17 Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE - Declaration of Conformity

CER_4000406200_00_000.pdf

Search Parts in this Series

120248 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION