

Home: > [Datasheet](#)

**Part Number: 502725-5522**

Image not available

**Status:** Active - Custom  
**Series:** [502725](#)  
**Category:** Molex Parts

**CHECK DISTRIBUTOR INVENTORY**

[Add to My Parts](#)

Go to [Part Detail](#)

Series image - Reference only

**Specifications & Other Documents:**

Documents not available online

Note - Please disable browser pop-up blockers to view documents on [www.molex.com](http://www.molex.com)

**Product Environmental Compliance**

Questions on Product Environmental Compliance? Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

[EU RoHS](#): ELV and RoHS Compliant

[China RoHS](#):

[REACH SVHC](#): Contains SVHC: No

[Low-Halogen Status](#): Low-Halogen

[Product Compliance Statement](#)

**Application Tooling**

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)

**Part Detail**

**COLLAPSE ALL**

▼ **General**

<b>Status</b>	Active - Custom
Category	Molex Parts
Series	<a href="#">502725</a>
UPC	883906156138

▼ **Physical**

Net Weight	40.342/g
------------	----------

▼ **Material Info**

**Molex Connectors**

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

**Other Products**

- Fiber Optic Products
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies
- Woodhead Electrical
- Solid State Lighting

**Resources**

- Contact Us
- Catalog
- Cross-Reference Industries
- Literature
- Product Name

**Company Info**

- About Us
- Careers
- ecocare
- Investors
- Press Room
- Shows & Events
- Supplier Portal

**Other Info**

- Feedback
- Help
- Legal Disclaimer
- View Mobile Site
- Privacy Policy
- Sitemap

**Stay Connected with Molex:**

