



**Part Number :** [5054134010](#)

**Product Description :** SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.90 or 1.00mm Mated Height, 2.00mm Mated Width, 40 Circuits, Armor Nail

**Series Number :** 505413

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents and Resources

### Drawings

[5054134010 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[5054139200-200.pdf](#)

[5054130000-001.pdf](#)

[5054130000-004.pdf](#)


[5054130000-005.pdf](#)

[5054130000-A00.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Compliant with Exemption 44; 33   |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)6375-DC (05 Nov 2025)  |

|         |   |
|---------|---|
|         | SCIP:bc5968db-5bed-458f-8beb-659ba1c3f73d |
| EU RoHS | Compliant per EU 2015/863                 |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | Board-to-Board Connectors  |
| Series         | 0.35, SSB RP   |
| Description    | SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.90 or 1.00mm Mated Height, 2.00mm Mated Width, 40 Circuits, Armor Nail |
| Application    | Board-to-Board   |
| Component Type | PCB Receptacle, Receptacle   |
| Product Name   | SlimStack  |
| UPC            | 889056306881   |

### Electrical

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.3A, 3.0A      |
| Voltage - Maximum             | 50V AC (RMS)/DC |

## Physical

|                                |                        |
|--------------------------------|------------------------|
| Circuits (Loaded)              | 40                     |
| Circuits (maximum)             | 40                     |
| Color - Resin                  | Black                  |
| Durability (mating cycles max) | 30                     |
| Glow-Wire Capable              | No                     |
| Mated Height                   | 0.90mm, 1.00mm         |
| Mated Width                    | 2.00mm                 |
| Material - Metal               | Copper Alloy           |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Gold                   |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 22.710/mg              |
| Number of Rows                 | 2                      |
| Orientation                    | Vertical               |
| Packaging Type                 | Embossed Tape on Reel  |
| PCB Locator                    | No                     |
| PCB Retention                  | Yes                    |
| Pitch - Mating Interface       | 0.35mm                 |
| Pitch - Termination Interface  | 0.35mm                 |
| Plating min - Mating           | 0.100µm                |
| Plating min - Termination      | 0.050µm                |
| Polarized to Mating Part       | No                     |
| Polarized to PCB               | No                     |
| Temperature Range - Operating  | -40° to +85°C          |
| Termination Interface Style    | Surface Mount          |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                 | Part Number            |
|---|------------------------|
| 0.35mm Pitch SlimStack Board-to-Board Plugs | <a href="#">505274</a> |
| 0.35mm Pitch SlimStack Board-to-Board Plugs | <a href="#">505417</a> |

---

This document was generated on Jan 05, 2026