

MICRO SWITCH
a Honeywell Division
FED.MFG.CODE 91929

SWITCH – BASIC

CATALOG LISTING
BE–2RB19–A2





NOTE
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø .139 MAX ON 1.000±.002 CENTERS

ANSI Y14.5M–1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL — DO NOT SCALE PRINT
OPERATING FORCE — — — —14–22 OZ	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
RELEASE FORCE — — — — —10 OZ MIN	25A 125 OR 250 VAC 1HP 125 VAC, 2HP 250 VAC PILOT DUTY 750VA 125, 250 OR 277 VAC 60/75 C (CU)	ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
DIFFERENTIAL TRAVEL — — —.0030–.0045		
OVERTRAVEL — — — — — —.094 MIN		WEIGHT .064 LB

REVISIONS

A	CO 73287–J	GRT 23 NOV 93
B	CO– 77590	LJF 15 JUN 94
C	CO– 95750–B	CSL 29 MAR 00

REPLACES X95564–BE
RELEASE NO. PR–20120
CATALOG LISTING BE–2RB19–A2
PAGE 1 OF 1
ISSUE 4

DRAWN	CHECK	
J W B 18 AUG 92	W J C 19 AUG 92	
FORMTEK		

Downloaded from Arrow.com.