Part Number : 638117400
Product Description : PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 26-22 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATS-6381174HM-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per ED/61/2018

Downloaded from Arrow.com.

	(27 June 2018)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 26-22 AWG
Comments	Field Repair, See Tooling Specification (PDF) Above; Type: 2C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	822350924245
Warranty Disclaimer	CAUTION: Molex tooling crimp

Downloaded from Arrow.com.

	specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	576.034/g

Applicable Parts

Description	Part Number
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 2.540µm Tin (Sn)	08500107
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 2.540µm Tin (Sn)	08500108
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 2.54µm Tin (Sn)	08500111
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 2.540µm Tin (Sn)	08500133
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 2.540µm Tin(Sn)	08500134
KK Trifurcon Crimp Terminal	08500183

Downloaded from Arrow.com.

7258, 26-22 AWG, Reel, Brass Tin (Sn)	
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Brass Tin (Sn)	08500185
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Tin(Sn)	08520124
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Tin (Sn)	08520125
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.38µm Selective Gold (Au)	08550105
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 0.38µm Selective Gold(Au)	08550106
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.76µm Select Gold (Au) over Gold Flash	08550123
KK 396 Crimp Terminal 2578, 26-22 AWG, Left Payoff Reel, Brass, 0.76µm Select Gold (Au) over Gold Flash	08550137
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.38µm Select Gold (Au) over Gold Flash	08560107
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 0.38µm Select Gold (Au) over Gold Flash	08560108
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Gold (Au)	08560123
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Gold(Au)	08560124
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au) over Gold Flash	08580125
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor	08580126

Downloaded from Arrow.com.

Bronze, 0.38µm Selective Gold (Au) over Gold Flash	
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 3.810µm Tin (Sn)	08600003
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 3.810µm Tin (Sn)	08600004
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.76µm Select Gold (Au) over Gold Flash	08650110
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	08650116
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au)	08650117
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Selective Gold (Au)	08650121
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Selective Gold (Au)	08650122

Downloaded from Arrow.com.