





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/12/04	
A		UPDATED DRAWING	1/17/19	HR/RC1



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 7 A AC/DC

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

-25°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X ± .10 .XX ± .020 .XXX ± .015			Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010		TITLE POWER LATCH HEADER, 6 PIN, STRAIGHT, PCB MOUNT	
APPROVALS			DATE		SIZE X	
DRAWN			SS		PART NO. PLHB-06-TS	
CHECKED					REV. A	
APPROVED					REF: S00016T	
					SCALE: NTS	
					SHEET 1 OF 1	