

Product Line

- Single Pair Ethernet >
- ZConnect >
- Socket
- Plug
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



ZA-20BFRS-BA0001

- Operating Temperature: -40°C ~ +110°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry

-
-
-
-
-

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search



ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >

- 0 +

Add to Cart

Inquiry

| Specifications | Download / CAD |
|-----------------------------------|---|
| Nominal Current 1A | Connector Type Receptacle PCB SMT 90 |
| Shielded Plastic, Non-shielded | No. of Contacts 20 |
| Connector Gender Female | Backshell N/A |
| Mating Style Quick Lock | IP Rating N/A |
| Assembly Style N/A | |
| <div> More Options</div> | |

People Also Bought

