



APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



Rev	AWO #	Description	Date	Appr
-		RELEASED	10/24/17	
A		UPDATED DRAWING	11/20/17	HR/IC

D




RECOMMENDED PCB LAYOUT

C



SECTION A-A



ASSEMBLY VIEW

**SPECIFICATIONS:****Material:**

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

**Plating:**

Tin over Nickel underplate overall

**Electrical:**

Voltage rating: 50 AC/DC

Current rating: 1 AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

**Temperature Rating:**

-25°C to +85°C

**Environmental:**

Lead free, RoHS compliant.



PACKAGED ON TAPE &amp; REEL

Positions: 02 thru 15

A= .059 [1.50] X No. of Spaces

B= .059 [1.50] X No. of Positions + .118 [3.00]

C= .059 [1.50] X No. of Positions + .024 [0.60]

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES HOLES  
 .X ± .10 ØX ± .10  
 .XX ± .020 ØXX ± .015  
 .XXX ± .015 ØXXX ± .010

## APPROVALS

## DATE

DRAWN

AY

CHECKED

CC

APPROVED

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

## TITLE

.059 [1.50] TOP ENTRY TYPE, SMT TYPE

## SIZE

PART NO.

15SH-A-XX-TS-SMT-T/R

REV.

A

REF: S00124T

SCALE: NTS

SHEET 1 OF 1