









LAYOUT FOR P.C.B

CONNECTOR SIDE VIEW



REV F – 2006-04-17

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE PRODUCT SPECIFICATION GS-12-446

NOTE-1: 2 PEGS AT EACH END ONLY
NOTE-2: CAVITY FOR CODING KEY MOUNTING AND CABLE CONNECTOR LATCH.
NOTE-3: IF SUFFIX "P" IS ADDED IN P/N PACKAGING IS IN TRAYS
BUT CONNECTOR MARKING IS WITHOUT "P"
EXAMPLE: HM1W53DTR400H6P, MARKED HM1W53DTR400H6
NOTE-4: P.C.B HOLES DEFINITION – SEE GS-12-446

SPECIFIC DATAS:
Visual inspection : 100%
- Marking failures
- Housing material failures
- Spoilt housing
- Stained housing
- Broken contacts (twisted or loosen)

TIN LEAD PART NUMBER
PART NUMBER HM1W53DTR400H6P

LEAD FREE PART NUMBER
PART NUMBER HM1W53DTR400H6PLF

0.76 um Au & LEAD FREE PART NUMBER
(F) PART NUMBER HM1W53DTR400HEPLF

rev	ecn no	dr	date
B	-	ROU	2001/11/21
C	LS05-001	MLE	2005/03/15
D	LS06-0095	LGO	2006/07/04
E	LS07-0012	MLE	2007/03/28
F	ELX-DG-19619	MIC	2014/12/03
-	-	-	-
-	-	-	-

European Views

www.fciconnect.com

surface ISO 1302 | tolerance std ISO 406 ISO 1101 | projection | mm

TOLERANCES UNLESS OTHERWISE SPECIFIED

Dr		
Eng	MICHAEL SONG	2014/12/03
Chr	ZHEN LUO	2014/12/03
Appr	COLLINS LU	2014/12/03

ANGULAR 0.XX ±2° | LINEAR 0.X ±0.1, 0.XX ±0.1, 0.XXX ±0.1

size A3 | Scale 2.5

ECN ELX-DG-19619

Product family METRAL | Spec ref -

title: METRAL STRAIGHT HEADER – 120 WAY SOLDER TAILS/WIDE BODY SP 400

dwg no C-8626-11106 | Rev. F

catalog no – | CUSTOMER | sheet 1 of 1

Copyright FCI.

Downloaded from Arrow.com.