

Splices

Selection Information



PIDG Nylon Insulated with Insulation Grip

- Copper inner sleeve
- Vibration resistant
- Barrel serrations
- Nylon insulation



PLASTI-GRIP Vinyl Insulated

- Funnel ramp entry
- Barrel serrations or dimples
- Vinyl insulation



SOLISTRAND Uninsulated

- Bell mouth
- Brazed seam
- Barrel serrations or dimples

Butt Splices

Wire Size	PIDG Nylon Insulated	PLASTI-GRIP Vinyl Insulated	SOLISTRAND Uninsulated
22-16	320559	34070	31818
16-14	320562	34071	31819
12-10	320570	34072	32151
8	—	—	34321
6	—	—	34322
4	—	—	34323
2	—	—	35189
1/0	—	—	36957
2/0	—	—	36958
3/0	—	—	36959
4/0	—	—	36960

Parallel Splices

Wire Size	PIDG Nylon Insulated	PLASTI-GRIP Vinyl Insulated	SOLISTRAND Uninsulated
22-16	—	—	34130
16-14	—	—	34137
12-10	—	—	34138
8	—	—	34318
6	—	—	34319
4	—	—	34320
2	—	—	35187
1/0	—	—	36946
2/0	—	—	36948
3/0	—	—	36909
4/0	—	—	36951