



Representative Image

## Catalog No. F10721NP

**Description:** NONINSL TERM No4AWG 5/16 BH NKLPLTD

**UPC No** 786210985091

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Non-Insulated Tubular Ring Terminal, Length 1.42 Inches, Width .62 Inches, Bolt Hole 5/16 Inch, Wire Range 4/4AN, Copper, Nickel Plated

### Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).

### Specifications

Voltage Rating	600 V
Material	Copper

### Classifications

Brand Name	Sta-Kon
------------	---------

### Dimensions

Wire Size	4/4AN
-----------	-------

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Flange shape	Ring shape
Slender flange model	N
Insulated	N
Material	Copper
Surface protection	Nickel-plated

**by ABB**

ETIM	EC001051 Tube cable lug for copper conductors
Number of mounting holes	1
AWG size	Other