

Hospital-Grade Outlet Strip *1584H Series*

15A | 125V | 5-15R-HG Outlets

Features



- Featuring a sturdy aluminum extruded case with a distinctive black powder paint coated steel cover.
- Designed to meet the special requirements for institutional and chronic care use with "Hospital Grade" white receptacles, line cord and plug.
- These devices are intended for non-patient connected indoor applications to providing power to electronic equipment.
- These devices are not intended to be used to supply power to life-support appliances, and not for use in critical care environments.
- Exceeds NEMA requirements for low leakage ground return and for withstanding impact or continuous physical shock without loss of grounding path continuity when plugged into properly grounded source receptacles.
- The white "Hospital Grade" receptacles are securely fastened onto the housing and interconnected with solidly bonded bus bars. All bus bars are double connected with a convection pressure sensitive clamp and safety screw.
- **Perfect for ground sensitive audio applications!**
- An additional grounding stud is provided on the case for any further external grounding requirements.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

Specifications

- Heavy duty 14 gauge cord - 14/3 SJT for extreme temperature ranges and integral clear molded "Hospital Grade" plug.
- Receptacles are NEMA 5-15R-HG.
- Complete with a 15 amp, 125 volt resettable circuit breaker to prevent accidental line overload.
- CSA certified, Standards C22.2 No. 308-18 Class 5842 08 (Hospital Grade Powerbars).
- TUVus certified to ANSI ES60601-1 (Medical Grade) & UL1363/1363A (Medical Grade) RPT's.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Rack Cabinet Vertical Mount Adaptor

Part No.	Overall Dimensions			Outlets	Cord Length (ft)
	Height	Width	Length		
1584T4DH6	2.33	2.12	10.18	4	6
1584T4DH	2.33	2.13	10.18	4	12
1584T6DH6	2.33	2.12	13.36	6	6

Part No.	Overall Dimensions			Outlets	Cord Length (ft)
	Height	Width	Length		
1584T6DH	2.33	2.13	13.36	6	12
1584T8DH6	2.33	2.12	16.51	8	6
1584T8DH	2.33	2.13	16.51	8	12

Replacement Mounting Foot (One Foot)

Part No.	1584MF
----------	--------

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.