**Part Number :** 1461850300
**Product Description :** Cellular Quad-band Flex Antenna, 15.00mm Width, 300.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
**Series Number :** 146185
**Status :** Active
**Product Category :** Antennas



## Documents and Resources

### Drawings

1461850300_sd.pdf

1461850100-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

AS-146185-100-001.pdf

PS-146185-100-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Antennas |
| Series | 146185 |
| Description | Cellular Quad-band Flex Antenna, 15.00mm Width, 300.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors |
| Component Type | Flexible Antenna with Cable |
| Function | Signal |
| Product Name | Multi-band Cellular-Wi-Fi |
| Protocol | Cellular |
| Type | Cellular Antenna, Internal |
| UPC | 889056549707 |

### Electrical

| | |
|---|---|
| Band#1 F_End (MHz) | 960 |
| Band#1 F_Start (MHz) | 824 |
| Band#2 F_End (MHz) | 2700 |
| Band#2 F_Start (MHz) | 1710 |
| Band#3 F_End (MHz) | 6000 |
| Band#3 F_Start (MHz) | 3000 |
| Electrical Connectivity | Cable |
| Peak Gain (dBi) | 1.1 @ 824 MHz, 2.6 @ 1710 MHz, 3.0 @ 3 GHz |
| Return Loss - S11 (dB) | < -4, < -6 |

Downloaded from Arrow.com.

| | |
|---|---|
| Total Efficiency | >56% @ 3 GHz, >59% @ 824 MHz, >61% @ 1710 MHz |

### Physical

| | |
|---|---|
| Cable Length | 300.00mm |
| Length | 84.00mm |
| Mounting Style | Adhesive |
| Net Weight | 1.561/g |
| Packaging Type | PET Film |
| Polarization | Linear |
| Radiation Pattern | Omnidirectional |
| Thickness | 0.10mm |
| Width | 15.00mm |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms | 734120110 |



Downloaded from Arrow.com.