

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301060115

Status:

Active

Overview:

Stringlights

Description:

Super-Safeway™ Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets with Guards, NEMA 5-15 Plug, Overall Length 15.24m (50.0')

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130106
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Literature Order No	987650-8055
Product Name	Super-Safeway™
Type	String Lights
UPC	78678879896
Woodhead	Yes
Physical	
Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	377
Guard Type	N/A
Height	107.95mm (4.250")
Length	15.24m (50.0')
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Rubber Molded
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Old Part Number	323526



EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

130106 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION