


HONEYWELL
PART NUMBER
111AT25
FAA-PMA 

REV	DOCUMENT	CHANGED BY	CHECK
13	0007018	KR 12AUG04	AK



- NOTES
- 1 - UNIT INCLUDES CATALOG LISTING V3-201 BASIC SWITCHES
 -  BASIC SWITCH NO. MARKED ON EACH BASIC SWITCH
 -  FLAT WHITE RESILIENT SILICONE RUBBER (50 DUROMETER APPROX)
 -  FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 111AT25 FOR FAA-PMA

ELECTRICAL DATA
CONTACT ARRANGEMENT S P D T (2)
15 A - 1/3 HP - 125 OR 250 VAC 1/2 A - 125 VDC; 1/4 A - 250 VDC

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ± 0.030
TWO PLACE .XX ± 0.015
THREE PLACE .XXX ± 0.005
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION


DRAWN	MBF	10MAR66
CHECK	LSD	11MAR66
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE ASSEMBLY - TOGGLE SWITCH			
SIZE B	TYPE I	DRAWING NAME 111AT25	REV 13
SCALE 1:1	SHEET 1 OF 1		