Part Number : 1301120124
Product Description : Magnetic Holder Base with Swivel
Series Number : 130112
Status : Active
Product Category : Portable Lighting Accessories
Engineering Part Number : 150



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Portable Lighting Accessories
Series	130112
Description	Magnetic Holder Base with Swivel
NEMA Configuration	N/A
Product Name	Woodhead
Type	Accessory
UPC	78678861620

Electrical

Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	N/A
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	N/A
Lamp Type	N/A
Length	N/A
Material - Guard	N/A
Net Weight	4939.972/g
Outlet	None
Packaging Type	Carton

Downloaded from Arrow.com.

This document was generated on May 20, 2026

Downloaded from Arrow.com.