



FLHTC0311-26-7 Product Details


FLHTC0311-26-7

TE Internal Number: 462469-000



Commercial Wire


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Cable Type = FlexLite HT
- Conductor Type = Tin-Plated Copper
- Conductor (Wire) Size = 26 AWG
- Temperature Range = -55 - 200 °C
- Color = Violet

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)


[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [HIGH TEMPERATURE HOOKUP WIRE, RADIATION-CROSSLINKED,...](#) (PDF, English)

Related Products:

- [Tooling](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Cable Type = FlexLite HT
- Color = Violet
- Cable Style = Primary
- Number of Conductors = 1

Configuration Features:

- Conductor (Wire) Size = 26 AWG
- Conductor Diameter (mm [in]) = 0.47 [0.019]

Electrical Characteristics:

- Number of Strands x AWG = 19 Strands x 38 AWG
- Voltage (VAC) = 600
- Resistance, Maximum (Ω /1000 ft@68°F) = 41.3

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Body Features:

- Conductor Type = Tin-Plated Copper
- Wire Type = Stranded
- Cable Diameter Range (mm [in]) = 0.77 - 0.84 [0.019 - 0.033]
- Nominal Weight (kg/km) = 1.89

Conditions for Usage:

- Temperature Range (°C) = -55 - +200

Product Availability:

- Region = Americas, Asia/Pacific

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

