

Han Q4/0 -M- Crimp



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 004 3051
Specification	Han Q4/0 -M- Crimp
HARTING eCatalogue	https://b2b.harting.com/09120043051

Identification

Category	Inserts
Series	Han [®] Q
Identification	4/0

Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	4
Details	Please order crimp contacts separately.
Details	Attention! Only for thermoplastic hoods/housings!

Technical characteristics

Conductor cross-section	1.5 ... 10 mm ²
Rated current	40 A
Rated voltage	830 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 PVVA8.E318390

Commercial data

Packaging size	10
Net weight	10.48 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140017146
eCl@ss	27440205 Contact insert for industrial connectors