




+ CONNECTORS



SCREENED



TE CONNECTIVITY (TE)  
TX40AZ00-2408

TX40AZ00-2408  
TE Internal Number: CW0599-000

Not EU RoHS or ELV Compliant  
[Find Compliant Alternatives](#)

✓ Active

↓ **PRODUCT DRAWING**  
English

Product Drawings

[Tinel-Lock Adapter](#)  
PDF  
**English**

Catalog Pages/Data Sheets

[5-1654025-5\\_sec6\\_Adapters](#)  
PDF  
**English**

Product Specifications

Product Specification

- [General Harness Repair Manual](#)  
PDF  
**English**
- [General Information Package For Tinel-Lock Adapters](#)  
PDF  
**English**
- [Adapter Finish Specifications](#)  
PDF  
**English**

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Termination Device Type

**Side-Entry Tinel-Lock Ring, Tinel-Lock Ring**

Connector Shell Size

**25, J**

Adapter Angle

**00**

	Style	Tinel-Lock
Body Features	TE Adapter Code	40
	Adapter Plating Material	ZnNi per ASTM B841 over Suitable Underplated & Chromate
	Adapter Entry Size	08
	Material	Aluminum
Dimensions	Cable Diameter Range	64 – 102 mm [ 25 – 4 in ]
Industry Standards	Connector Detail Specification Number	D38999/20, D38999/24, D38999/26, D38999/40, D38999/42, D38999/46, D38999/47
Other	Connector General Specification Number	MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W
Product Compliance	<div>Statement of Compliance</div> <div>PDF</div> <div>VIEW ALL PRODUCT COMPLIANCE</div>	