

PZ 4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for wire-end ferrules, 0.5mm ² , 4mm ² , Trapezoidal crimp
Order No.	901250000
Type	PZ 4
GTIN (EAN)	4008 190090920
Qty.	1 items

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	425.6 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	(1)Crimping tool	Version	Mechanical, without interchangeable inserts
------------------------	------------------	---------	---

Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Conductor cross-section, max. AWG	AWG 12
Conductor cross-section, min. AWG	AWG 21	Crimping range, max.	4 mm ²
Crimping range, min.	0.5 mm ²		

tool data crimping

Drive	mechanical	Wire end ferrules cross-section, max.	4 mm ²
Wire end ferrules cross-section, min.	0.5 mm ²	Crimping type/profile	Trapezoidal crimp

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

PZ 4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

