



HONEYWELL  
PART NUMBER  
21SM289-T  
PRODUCT CODE  
TXL8706

REV	DOCUMENT	CHANGED BY	CHECK
B	0038444	KVS 09APR08	ASD



NOTES

- ▲ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2- TERMINALS ARE GOLD PLATED FOR SOLDERING

RELEASE NO.	-
REPLACES	X98022 - SM

CHARACTERISTICS	
OPERATING FORCE	3 - 5 OZ
RELEASE FORCE	1 OZ MIN
DIFFERENTIAL TRAVEL	.004 MAX
OVERTRAVEL	.005 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT SPDT			
30 VOLTS DC RATING			
SEA LEVEL		50,000 FT	
LOAD	28 VDC	115 VAC 60 CPS	28 VDC
RESISTIVE	5.0 AMP	5.0 AMP	5.0 AMP
INDUCTIVE	3.0 AMP	5.0 AMP	2.5 AMP
LAMP	2.4 AMP	1.5 AMP	2.4 AMP

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION

DRAWN	VK	18FEB 08
CHECK	RJ	18FEB 08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

<b>Honeywell</b>			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	21SM289-T	B
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1