Hello, We use cookies to create the most secure and effective website possible. By using this site, you consent to the use of cookies. See full details in our Privacy Statement.

Click here to not show this message again


64AT22-1

Overview

MICRO SWITCH AT Series Toggle Switch, 4 pole, 3 position, Quick Connect terminal, Standard Lever.


MICRO SWITCH AT toggle switches provide a compact

View More



view all 64AT22-1 literature
view distributor inventory
sample request
email support
get support
email sales
find a distributor
email this page

Technical Specifications

Product Type	MICRO SWITCH Toggle	Ampere/Voltage Range (Resistive Load)	0.1 A to 7.0 A at 0.5 Vdc to 28 Vdc
Circuitry	4PDT	Action	3 position
Circuitry/Operating action		Mounting	Bushing 15/32 in
Termination	Quick Connect	Comment	FAA-PMA approved
Availability	Global	UNSPSC Code	39122211

View More

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
AT Series Toggle Switch Assemblies	Catalog Information	English	427KB
Sensors and Switches in Oil Rig Applications	Application Note	English	7MB
Flight Deck Toggle Switches	Application Note	English	185KB
Oil and Gas Brochure	Brochure	English	4MB

View More

Product Features

- Gold or silver contacts
- Choice of sealed bushing
- Standard or pull to unlock toggle lever
- Short behind-panel depth
- Solder or quick connect termination
- 2,4, 6, or 8 SPDT precision basic switches
- 2 or 3 position, momentary or maintained action

Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
  Test instruments

Downloaded from Arrow.com.

- Agricultural machinery
- Process control
- Medical instrumentation

COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.

Downloaded from Arrow.com.