



Part Number : [462350004](#)
Product Description : Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with .0.76µm Selective Gold (Au) over Nickel (Ni), 30-26 AWG, without Lubricant
Series Number : 46235
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings
[462350004_sd.pdf](#)
[PK-46235-001-001.pdf](#)

Specifications
[PS-46235-001-001.pdf](#)
[430450006-TS-000.pdf](#)
[TS-46235-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	46235
Description	Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with .076µm Selective Gold (Au) over Nickel (Ni), 30-26 AWG, without Lubricant
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Up to 50% reduction in mating force
Product Name	Micro-Fit RMF
UPC	800756683614

Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

Physical

Durability (mating cycles max)	40
Gender	Female
Material - Metal	Copper-Zinc-Tin
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.088/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size (AWG)	26, 28, 30

Wire Size mm ²	N/A
---------------------------	-----

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Receptacle Housings	<u>43025</u>
Micro-Fit 3.0 Single Row Receptacle Housings	<u>43645</u>
Micro-Fit BMI Dual Row Receptacle Housings	<u>44133</u>
Micro-Fit TPA Receptacle Housings	<u>172952</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>11030043</u>
FineAdjust Applicator for Micro-Fit 3.0 Low Force Crimp Terminals, 30-26 AWG Stranded Copper Wires	<u>2037024900</u>
PremiumGrade Hand Crimp Tool for Low Force Micro-Fit 3.0 Terminals, 30-20 AWG	<u>638192900</u>
T2 Terminator Tooling Die for Crimp Terminal, 30-26 AWG Wire	<u>639101300</u>

This document was generated on Mar 14, 2025