




PRODUCT NUMBER


PITCH

KExx33x0A0J0G

3.81 mm



SECTION H-H

RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item a Terminal housing: Thermoplastic (UL94V-0)
- Item b Pin: Copper Tin plated

Electrical:

- Voltage rating: 300V
- Current rating: 5.5A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C ±5°C/5 Sec
- Safety Approval: cULus

DIMENSION

Dim.L	(N/2-1) × 3.81+4.4		
Dim.P	(N/2-1) × 3.81		
Dim.A	(N/2-1) × 3.81		

N=Number of poles

poles	Dim.L	Dim.P	Dim.A
2×2P-2×5P	±0.20	±0.15	±0.15
2×6P-2×16P	±0.30	±0.25	±0.25
2×17P-2×24P	±0.40	±0.30	±0.30

PART NO.: KE xx 3 3 x 0 A0J0 G

Solid block

No. of poles

04 2x2poles

06 2x3poles

... ..

48 2x24poles

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

9 White(RAL1102)

C Green(RAL6018/U)

 RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface	tolerance	projection	product family	
ltr	ecn	no	dr	date	ASME Y14.5	ASME Y14.5	TERMINAL BLOCK	
					tolerances unless otherwise specified		title	
					angles	X.±0.5	TERMINAL BLOCK	
					parallel	X.X±0.3	PLUGGABLE SOCKET, VERTICAL, W/LATCH HOLDER	
					X°±1°	X.XX±0.1	scale	
					dr	EVIN ZHONG 042414	dwg no	
					enrg	EVIN ZHONG 042414	sheet 1 of 1 size	
					chr	HANKE FENG 042414	KExx33x0A0J0G	
					appd	SHI JUN 042414	type	
							CUSTOMER Drawing	
sheet index	revision	A						
sheet	sheet	1						