





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

.145 ± .007 Ø
[3.7 ± 0.18]



PANDUIT PART NO. **	'L' in / (mm)	RECOM'D FASTNER	WEIGHT lbs 100 (g) pcs
RAFCB11-S6	1.75 (44.4)	#6 (M3)	0.64 (292)
RAFCB12-S6	2.78 (70.6)		0.87 (394)
RAFCB13-S6	3.81 (96.8)		1.06 (479)

- NOTES:
- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
 - MATERIAL: 6/6 NYLON
COLOR: BLACK
 - USE THE FOLLOWING CABLE TIES WITH ANY OF THESE PRODUCTS:
M=MINATURE, I=INTERMEDIATE, S=STANDARD



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYER: G00239FZ_PB_RAFCB1_00

PANDUIT

CORP. TINLEY PARK, ILLINOIS

RIGHT ANGLE FLAT CABLE BASE

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE 1/15/04

SEE NOTE 2

DRAWING NO.

G00239KZ

DWG

A
SIZE

R	1/15/04	JAD		INITIAL RELEASE	G00239KZ	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	