








APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/10/15	
A		UPDATE DIM.	9/15/15	AY/MY



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Copper Alloy, Matte Tin plated

Plating:

Gold over Nickel underplate in contact area

Electrical:

Current rating: (1, 5 Pin): 1.8A Max, (2, 3, 4Pin): 1.0A Max.

Contact resistance: 30 milliohms max.

Insulation resistance: 100 Megohms min.

Dielectric withstand voltage: 100 VAC for 1 minute

Temperature Rating:

Operating temperature: -30°C to +80°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	AY	8/10/15
CHECKED	YC	8/10/15
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
MICRO USB, TYPE AB, SINGLE PORT, FEMALE
TRUE SMT TYPE, W/PEG, TAPE & REEL

SIZE	PART NO.	REV.
X	MCR-AB-S-RA-TSMT-P-CS2-T/R	A
REF: S00126T		SCALE: NTS
		SHEET 1 OF 1