

 [Live Product Chat](#)



✓ Active

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

- Cable Assembly
- Fiber Type = 62.5/125
- Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)
- ST Connector
- Multimode

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Product Drawings: • FOMM62.5 LEAD 2.5S ST - ST (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Related Products: • Tooling
--	--

[List all Documents](#)

Product Type Features: • Product Type = Cable Assembly • Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet) • Connector = ST Termination Related Features: • Mode = Multimode • Insertion Loss (dB) = 0.30 Body Related Features: • Fiber Type = 62.5/125 • Cable Diameter (mm [in]) = 2.40 [.094] • Number of Fibers = 1 • Flammability Rating = Low Smoke Zero Halogen (LSZH) • Cable Color = Orange • Length (M [ft]) = 1.00 [3.281] • Ferrule Material = Ceramic	Contact Related Features: • Boot Body Style - Left = Standard • Boot Color - Left = Black • Boot Body Style - Right = Standard • Boot Color - Right = Black • Fibre Channel = No Configuration Related Features: • Cable Type = Simplex • Cable Buffering = Tight Buffered Easy Strip • Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180° Industry Standards: • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not relevant for lead free process Other: • Brand = AMP
--	---