

# Specifications

## Eaton CL1208-3-100TR-R

Eaton CL1208 inductor, 100 nH, 0.45 mΩ resistance, Three-phase

### General specifications

<b>PRODUCT NAME</b>	Eaton CL1208 inductor
<b>CATALOG NUMBER</b>	CL1208-3-100TR-R
<b>UPC</b>	051712523608
<b>PRODUCT LENGTH/DEPTH</b>	18 mm
<b>PRODUCT HEIGHT</b>	8 mm
<b>PRODUCT WIDTH</b>	11.5 mm
<b>PRODUCT WEIGHT</b>	6.25 g
<b>COMPLIANCES</b>	RoHS Compliant
<b>PRODUCT TYPE</b>	Inductor

## Product specifications

<b>TYPE</b>	Multi-phase coupled inductor
<b>MOUNTING</b>	SMT
<b>PHASE</b>	Three-phase
<b>ISAT</b>	18 A
<b>PACKAGE QUANTITY</b>	300
<b>MATERIAL</b>	Ferrite
<b>CONTACT CONFIGURATION</b>	Six-pin
<b>TEMPERATURE RATING</b>	-40 to 125 °C
<b>RESISTANCE</b>	0.45 mΩ
<b>TERMINALS</b>	Six
<b>INDUCTANCE</b>	100 nH
<b>SERIES</b>	CL1208

## Resources

CATALOGS	<a href="#">Magnetics short form catalog</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CL1208-3-100TR-R</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

