

## Plastic label with drill hole - EMLP 30(45X10)R - 0801855

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plastic label with drill hole, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 45 x 10 mm

The figure shows the white version

### Product Features

- ✓ The self-adhesive markers are ideal for marking electrical buttons
- ✓ High level of resistance to chemical and mechanical influences
- ✓ Quick and inexpensive marking with THERMOMARK ... printers

### Key commercial data

|                                      |           |
|--------------------------------------|-----------|
| Packing unit                         | 1 pc      |
| Weight per Piece (excluding packing) | 640.0 GRM |
| Custom tariff number                 | 39199000  |
| Country of origin                    | Germany   |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 46 mm |
| Width (a)  | 46 mm |

#### Ambient conditions

|                                 |                                 |
|---------------------------------|---------------------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C               |
| Recommended storage conditions  | 21 °C / 50 % relative humidity. |

#### General

|                                     |                                |
|-------------------------------------|--------------------------------|
| Color                               | white                          |
| Components                          | free from silicone and halogen |
| Material                            | Polyester                      |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1)    |
| Number of individual labels         | 500                            |
| Number of individual labels per row | 1                              |

## Plastic label with drill hole - EMLP 30(45X10)R - 0801855

### Technical data

#### General

|                                                                     |                               |
|---------------------------------------------------------------------|-------------------------------|
| Adhesive                                                            | Acrylic                       |
| Printability                                                        | Thermal transfer              |
| Device                                                              | 5146477 THERMOMARK ROLL       |
|                                                                     | 5146723 THERMOMARK ROLL X1    |
|                                                                     | 5146257 THERMOMARK S1.1       |
|                                                                     | 5146231 THERMOMARK X1.2       |
| Ink ribbon                                                          | 5145384 THERMOMARK-RIBBON 110 |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02          |
| Result                                                              | Test passed                   |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03  |
| Test duration                                                       | 96 h                          |
| Wipe resistance test result                                         | Test passed                   |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02     |
| Test duration                                                       | 96 h                          |
| Salt spray testing result                                           | Test passed                   |
| Alternating condensation climate with SO2 test specification        | Following DIN 50018:2013-05   |
| Climate level                                                       | AHT 1.0 S                     |
| Cycles                                                              | 2                             |
| Condensation test result                                            | Test passed                   |
| Wipe resistance of test specification inscriptions                  | DIN EN 60068-2-11:2000-02     |
| Result                                                              | Test passed                   |
| Foil strength                                                       | 50 µm                         |
| Adhesive strength                                                   | 20 µm                         |
| Marking mounting type                                               | Adhesive                      |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190218 |
| eCl@ss 4.1 | 24190218 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

## Plastic label with drill hole - EMLP 30(45X10)R - 0801855

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

Phoenix Contact 2014 © - all rights reserved  
<http://www.phoenixcontact.com>