
FOR-1350 Rev.1.0

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE


SR-M12X-XXP-MM-SF7003-00A(H)


Coding: A,B,D — Pin number: 04,05,08


8pin A Coding





Pin Assignments
Front View

















Panel Mounted

NOTES:

1. Rated voltage/current : 4pin A: 250V / 4A
   5pin A: 60V / 4A
   8pin A: 30V / 2A
   5pin B: 60V / 4A
   4pin D: 250V / 4A
2. Withstanding voltage : 4pin A: AC1500V/1Min
   5pin A: AC1120V/1Min
   8pin A: AC500V/1Min
   5pin B: AC1120V/1Min
   4pin D: AC1500V/1Min
3. Levels of protection: IP67
4. Wire connection mode: soldering(PCB)
5. Operating temperature: −40℃~+105℃
6. For Panel Thinkness Max: 4.5mm
7. RoHS Compliance

4pin A Coding	4pin D Coding	5pin A Coding	5pin B Coding
			
Pin Assignments Front View	Pin Assignments Front View	Pin Assignments Front View	Pin Assignments Front View





DETACHED LISTS	PART NO.: SRM12XXXPMMSF700300AH	DEGSON® 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
	APPD:	NAME: SR-M12X-XXP-MM-SF7003-00A(H)	
	CHKD:		
	DRFT: SQ 2019.03.26	TITLE: CUSTOMER DRAWING	REV: D0−1
	THIRD ANGLE PROJECTION	DRAWING NO.: XXXXXXX−XX−CXX	SHEET: 1/1
		MM (INCH) DO NOT SCALE DRAWING	SCALE: 1:1

Downloaded from Arrow.com.