

Specification Sheet

Part Number: 151-00459



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip with Round Fir Tree, 0.7 - 5.1 mm Panel Thick., 6.5 - 7.0 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Article Number 151-00459

Type FT6LG.JAE.CONNECT.TS

Color Black (BK)

Quantity Per pack

Product Description Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description Connector Clip with Round Fir Tree, 0.7 - 5.1 mm Panel Thick., 6.5 - 7.0 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Global Part Name FT6LG.JAE.CONNECT.TS-PA66HIRHS-BK

Compatible For Third Party Product 2 The connector clips can be used to hold JAE-connector.

Length L (Imperial) 0.95

Length L (Metric) 24.0

Fixation Method Fir tree for round holes

Width W (Imperial) 0.63

Width W (Metric) 16.0

Height H (Imperial) 0.7

Height H (Metric) 17.9

Panel Thickness Min (Imperial) 0.03

Panel Thickness Max (Imperial) 0.20

Panel Thickness Min (Metric) 0.7

Panel Thickness Max (Metric) 5.1

Mounting Hole Diameter D (Imperial) 0.26 - 0.28 "

Mounting Hole Diameter D (Metric) 6.5 - 7.0 mm

Mounting Hole Diameter D Min (Imperial) 0.26

Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	16
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)