Part Number : 1301530132
Product Description : Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA 5-20, 20A, 120V, 1.83m (6.0') Cord Length
Series Number : 130153
Status : Obsolete
Product Category : Power Distribution
Engineering Part Number : 20052-6A



Documents and Resources

Drawings

1301530132_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA 5-20, 20A, 120V, 1.83m (6.0') Cord Length
Enclosure Rating	NEMA 4X
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678888291

Agency

UL	E66308

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Automatic
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	N/A

Physical

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	1.83m (6.0')
Cord Type	12/3 SJEOOW
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable

Obsolete

Downloaded from Arrow.com.

Number of Receptacles	1
Packaging Type	Bag
Receptacle Type	N/A

This document was generated on Sep 26, 2026

Obsolete

Downloaded from Arrow.com.