




**Part Number :** [2045320301](#)  
**Product Description :** Micro-Lock Plus  
Receptacle Housing, 1.25mm Pitch, Single  
Row, with Positive Lock, 3 Circuits, Low-  
Halogen, Black  
**Series Number :** 204532  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources


**Drawings**  
[2045320301\\_sd.pdf](#)

**3D Models and Design Files**  
[2045320301.dxf](#)  
[2045320301.pdf](#)  
[2045320301\\_stp.zip](#)

**Specifications**  
[5055650000-AS-000.pdf](#)  
[2045329200-200.pdf](#)  
[2045320000-PS-000.pdf](#)  
[2045320001-PS-000.pdf](#)  
[2045320002-PS-000.pdf](#)  
[2045321000-PS-001.pdf](#)  
[2045321001-PS-000.pdf](#)  
[5055650003-PS-000.pdf](#)  
[2045320000-PS-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

## Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Housings
Series	204532
Description	Micro-Lock Plus Receptacle Housing, 1.25mm Pitch, Single Row, with Positive Lock, 3 Circuits, Low-Halogen, Black
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Lock Plus
UPC	191128418256

#### Agency

CSA	LR19980
UL	E29179

#### Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester

Net Weight	78.170/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers with Potting Capability	<u>205957</u>
1.25mm Pitch, Micro-Lock Plus Single Row Plug Housings	<u>214525</u>
Micro-Lock Plus Vertical, Single Row, Through Hole Headers	<u>220097</u>
Micro-Lock Plus Right-Angle, Single Row, Through Hole Headers	<u>220098</u>

### Use with Part(s)

Description	Part Number
Micro-Lock Plus Female Crimp Terminals	<u>505431</u>

---

This document was generated on Apr 24, 2025