




- NOTES:
- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST.
- 2.) WHITE LABEL CONTENT:

CWK/YR-XXXXX-X-XX
HARTING P/N

BLACK FONT; FONT HEIGHT: 3.5.

- 3.) CABLE SHOULD BE FOLDED MANY CIRCLES ACCORDING TO TOTAL CABLE LENGTH AND PACKED BY A PLASTIC BAG (QTY ACCORDING TO ACTUAL CONDITION),STICK THE LABEL WITH P/N,QTY AND LOT NUMBER ON IT,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION).
- 4.) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

Part-No.	Length-L
33 18 243 150 0069	1500mm
33 18 243 100 0057	1000mm
33 18 243 050 0055	500mm

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		
			Det.	Name	Scale /	SEK 40P FEMALE DOUBLE END FLAT TWIST CABLE ASSY,L=XM		
			Detail	Andrew				
			Insp.					
			Stand					
ZHUHAI HARTING LIMITED 						TB 33 18 0002 .00		
Mod.	Da.t.	Name				Sub		
						Page		