






LAYOUT FOR P.C.B
scale : 2.5



NOTES:

1. MATERIAL : BODY : LCP UL94-V0
   : CONTACT : COPPER ALLOY.
2. FOR PLATING PERFORMANCE REFER DRAWING # 10159409 G
3. METALIZED HOLE DEFINITION, SEE GS-12-447.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47- 0004
5. STANDARD PACKING IS IN TUBES,
   BUT IF SUFFIX "P" IS ADDED IN P/N PACKAGING IS IN TRAYS
   BUT CONNECTOR MARKING IS WITHOUT "P"
   EXAMPLE: HM1xxxxxxxxHXPLF , MARKED HM1xxxxxxxxHXLF
6. A G SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

X REFER DRAWING # 10159409 G

SPECIFIC DATAS:

Visual inspection : 100%
- Marking failures
- Housing material failures
- Spoilt housing
- Stained housing
- Broken contacts (twisted or loosen)

PART NUMBER	HM1S52FER400HXLF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE GS-12-447

ltr	ecn no	dr	date
E	LS07-0266	MLE	2007-11-09
F	DG09-0367	TER	2009-11-25
G	ELX-I-38915	MINI	2020-10-16

mat'l. code	NOTE 1	
surface ISO 1302	58	
tolerance ISO 406 ISO 1101		
tolerances unless otherwise specified		
angles	0°±2°	
linear	0.X±0.3	
	0.XX±0.13	
	0.XXX±0.050	
projection		
MM		
scale	1:1	
dr	PERRICHOT	2001-01-26
engr	ARUN	2020-10-16
chr	ALEX BABU	2020-10-16
appd	SANOJ	2020-10-16
sheet index	revision G / sheet 1	
product family	METRAL	
title	METRAL FEMALE 5 ROWS 60 WAY PRESS FIT	
dwg no	C-8626-11112	
sheet	1 of 1	
size	A2	
type	Product Customer Drawing	

© 2016 AFCI

Downloaded from Arrow.com.