



**Part Number :** [1501811016](#)  
**Product Description :** Standard .062"+ Female  
Terminal, 16-18 AWG, Tin (Sn) Plated, Reel  
**Series Number :** 150181  
**Status :** Active  
**Product Category :** Crimp Terminals




## Documents & Resources

**Drawings**  
[Drawing 1501811016\\_sd.pdf](#)  
[Packaging Design Drawing PK-150180-001-000.pdf](#)

**Specifications**  
[Application Specification 1501760001-AS-000.pdf](#)  
[Product Specification 1501760001-PS-000.pdf](#)  
[Test Summary 1501760001-TS-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	150181
Description	Standard .062"+ Female Terminal, 16-18 AWG, Tin (Sn) Plated, Reel
Application	Power, Wire-to-Wire
Product Family	Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Product Name	Standard .062"+
UPC	889056491112

### Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	400V

### Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.145/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.70-2.10mm
Wire Size (AWG)	16, 18
Wire Size mm <sup>2</sup>	N/A

---

## Use with Part(s)

Description	Part Number
Standard .062"+ Single Row Receptacle Housings	<u>150178</u>
Standard .062"+ Dual Row Receptacle Housings	<u>150179</u>

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	<u>11030002</u>
Hand Crimp Tool for EconoLatch Male and Female Terminals, 16-18 AWG UL1061 and 18 AWG UL1007 wires	<u>638280600</u>
FineAdjust Applicator for EconoLatch Crimp Terminals, 16-18 AWG	<u>639036100</u>
FineAdjust Applicator for EconoLatch Crimp Terminals, 18 AWG	<u>639036200</u>

---

This document was generated on Mar 26, 2024