

Products

Services



3G/4G Module

LM_PLS8-X

4G Module

Key Features

Download

[iCom Product List_Q32017_3G 4G_CN_LM_PLS8-X.pdf](#)

Product Specification

Solution	Qualcomm MDM9215
Air Interface	LTE (US)
Data Speed (Mbps)	- DL: 100Mbps - UL: 50 Mbps
Dimension (mm)	51.0(L)×30.0(W) × 5.0(H)
Frequency (MHz)	- GSM/GPRS/EDGE 850/ 900/ 1800/ 1900 - HSPA/UMTS 850/AWS/1900 - FDD-LTE LTE Cat. 3 700/ 850/ AWS(1700/2100)/1900
Antenna	50 Ohms
Diversity	UMTS/LTE
MIMO	2x2
Control Option	AT command
Option	- GPS GLONASS(Standalone GPS and GLONASS) - SIM Holder

OS compatibility	▶ Windows®8 ▶ Windows®7 ▶ Linux ▶ Android
Certification	▶ R&TTE, FCC, IC, UL, GCF, PTCRB
Power Supply	▶ 3.0V - 3.6V
Operation Temperature	▶ -40° to +85°C