








Specifications
 Current Rating:1.0A AC,DC
 Voltage Rating:50V AC,DC
 Contact Resistance:20m ohm. Max.
 Insulation Resistance:1,000M ohm. Min.
 Withstanding Voltage:500V AC/minute.
 Operating Temperature Range:-40°C to +105°C

Materials:
 Insulator:Nylon 9T(UL94V-0)
 Insulator Color:Black
 Contact: Brass
 Plating:Gold Plated

Circuits	DIM		Circuits	DIM	
	A	B		A	B
6	2.54	18.16	34	20.32	35.94
8	3.81	19.43	40	24.13	39.75
10	5.08	20.70	44	26.67	42.29
16	8.89	24.51	50	30.48	46.10
20	11.43	27.05	60	36.83	52.45
26	15.24	30.86	68	41.91	57.53
30	17.78	33.40			

MATING PART
 3230-XX-0101-00

MATING PART
 3230-XX-0102-00



PCB Layout

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology		D
				CHECKED:	UNIT: MM	DESCRIPTION: 1.27mm Shrouded Header SMD Type	SIZE A4	
B	30-Mar-2020				SCALE:1:1			
A	30-Aug-2018			APPROVAL:	SHEET: 1 / 1	PART NO: 3210-XX-003-12-00-TR		
REV	DATE	FILE	BY		PROJECTION: 