



# YAV2CRS1NK, Uninsulated Right Angle Ring Terminal For 2 AWG, 1-Hole, 1/4" Stud, Nickel Plated

By Burndy  
Catalog # [YAV2CRS1NK](#)



Uninsulated Right Angle Ring Terminal For 2 AWG (Nickel Plated)

## Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

## Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	Yes

## Conductor

Conductor - Copper Str Aircraft Size	AN 2
Conductor Size	2 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

## Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Dimension - B Length fraction	5/8 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.62 in
Dimension - Outside Diameter inch	0.47 in
Dimension - Z inch	0.34 in
Dimension - Pad Width inch	0.68 in
Dimension - G inch	1 in
Physical Attribute - Tongue Angle	90 Degree
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size mm	7 mm
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	1/4 in
Dimension - Length Overall inch	1.27 in
Dimension - N inch	0.33 in

## General

Die Index	41
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810267936
Material	Copper
Plating Type	Nickel
UPC	781810267936

## Logistics

Minimum Pack Quantity	200
Carton Quantity	200
Pallet Quantity	69600

## Product Assets

[Catalog \[English\]](#)

