R-Series




The R-Series Curvette single pole miniature snap-in rocker switches are available with momentary, rocker, paddle & Visi-Rocker type actuators. These aesthetically pleasing switches are compatible with a range of standard panel cutouts. Electrical ratings, with international approvals, are available up to 16 amps.

Specifications

- Certifications*: UL, CSA, VDE, TUV, SEMKO, DEMKO, NEMKO, FIMKO, SEVand BEAB
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Polyester or Nylon

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



MOUNTING HOLE
Panel Thickness: .025 min - .187 max.
Specific cutout dimension range dependent on panel thickness and material. Consult factory.

R A 91 1 - V B - B - 0 - V

SERIES

R SINGLE POLE

CIRCUIT

A OFF-NONE-ON
B ON-NONE-ON
C ON-OFF-ON
Available w/ratings 21, 23, 58, & 91 only
D OFF-NONE-(ON)
Available w/rating 22 only
AD OFF-NONE-ON
Double Insulation
BD ON-NONE-ON
Double Insulation
CD ON-OFF-ON
Double Insulation
Available w/ratings 21 and 58 only

RATING[1]

20 10A 250VAC
16A 125VAC
3/4HP 125-250VAC
21 10A 250 VAC
16A 125VAC
22 8A 250VAC
12A 125VAC
1/2HP 125-250VAC
23 10A 250VAC
16A 125VAC
1/2HP 125-250VAC
58 5A 277VAC
10A 125VAC
10A 30V
8A 14VT
90 10A 250VAC
16A 125VAC
3/4HP 125-250VAC
10(4)A 250VACμ T85
91 10A 250VAC
16A 125VAC
10(4)A 250VACμ T85

TERMINATION

0 SOLDER LUG
1 .250TAB (QC)
5 WIRE LEAD

ACTUATOR STYLE

M MOMENTARY ROCKER
P PADDLE
R ROCKER
V TWO COLOR VISI-ROCKER

ACTUATOR COLOR[2]

B BLACK
W WHITE

BASE COLOR[2]

B BLACK
W WHITE

ROCKER FACE LEGEND

	MOLDED-IN[3]	INK TRANSFER STAMP[4]
0	NO LEGEND	**0**
1	OFF-ON (VERTICAL)	**A**
2	OFF-ON (HORIZONTAL)	**B**
8	O-I (HORIZONTAL)	**D**
9	O-I (VERTICAL)	**E**
	ON-OFF (VERTICAL)	**F**
	ON-OFF (HORIZONTAL)	**G**
	DUAL LEGEND: OFF O-I ON (VERTICAL)	**H**

COLOR OF MOLDED-IN LEGEND AND/OR VISI-ROCKER END[2]

N NOT APPLICABLE
B BLACK
V VISI-RED
W WHITE

NOTES:
Shading indicates standard configurations.
Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.
1 Additional ratings are available. Consult factory.
Rating 22 must use circuit D only and momentary rocker.
2 Matte finish is standard. Custom colors are available. Consult factory.
3 Molded-in Legend available only with Visi-Rocker option.
4 White is standard with dark actuators; black is standard with light actuators.

Downloaded from Arrow.com.