



ITEM NO.	DESCRIPTION	QTY.
1	SHELL	1
2	INSULATOR	1
3	MAGNET	1
4	POGO PIN	1


REVISIONS			
REV.	DESCRIPTION	DATE	BY
1	ORIGINAL	DRAWN DATE	











RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05

SPECIFICATIONS

CURRENT RATING:	3A
VOLTAGE RATING:	12V
WITHSTANDING VOLTAGE:	500V
INSULATION RESISTANCE:	1000MΩ MIN FOR 1 MIN
CONTACT RESISTANCE:	50mΩ MAX
TEMPERATURE RANGE:	-25°C TO 80°C
INSULATOR MATERIAL:	HTN
INSULATOR COLOR:	BLACK
CONTACT MATERIAL:	BRASS
CONTACT PLATING:	5µ" GOLD PLATING
MAGNET MATERIAL:	N52
MATING CYCLES:	10000
MATING PARTS:	MPM-V00-802-2P14-E00 MCM-Y00-0E2-2P14-BH0 MCM-Q00-0E2-2P14-BH0

NOTE:IR REFLOW AND WAVE SOLDERING NOT RECOMMENDED AS THE PROCESSES CAN DEMAGNETIZE THE CONNECTOR MAGNETS.

RoHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC, AND SHALL NOT BE REPRODUCED , OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN BY	V.K.
DRAWN DATE	08/27/2025
CHECKED BY	R.S.M.
CHECK DATE	08/27/2025

TOLERANCES	
.X	±0.3
.XX	±0.2
.XXX	±0.1

ALL DIMENSIONS AND TOLERANCES IN MM

FEMALE CONNECTOR, CIRCULAR, 8 MM DIA, 2 POSITIONS

PART NUMBER	MPF-V00-802-2R14-E00		
MATERIAL		SIZE	A
		REVISION	1
SCALE	3.5:1	SHEET	1 OF 1

Downloaded from Arrow.com.