


MF480272B43-BF
(480(RGB) * 272 DOTS)



EVERBOUQUET / WAYTON

EXTERNAL DIMENSION



KEY SPEC. & INTERFACE PIN CONNECTION

Item	Description	Unit
Screen Size (Diagonal)	4.3	inch
Driver IC	HX8227-A01 & HX8655-A	--
Module Size	105.5 x 67.2 x 3.95	W x H x D (mm)
Active Area	95.04 x 53.856	W x H (mm)
LCD Type	Transmissive a-Si TFT	--
Dot Number	480x RGB x 272	W x H (dots)
Pixel Size	0.198 x RGB x 0.198	W x H (mm)
Pixel Arrangement	RGB Stripe	--
Viewing Direction	6	o'clock
Viewing Angle (R/L/U/D)	(45/45/35/15)	degree
Contrast Ratio	250:1	--
Color Saturation (NTSC)	50%	--
Response Time (Tr+Tf)	50ms (TYP)	ms

PIN NO	1	2	3	4	5	6	7	8	9	10
SYMBOL	GND	GND	VDD	VDD	R0	R1	R2	R3	R4	R5
PIN NO	11	12	13	14	15	16	17	18	19	20
SYMBOL	R6	R7	G0	G1	G2	G3	G4	G5	G6	G7
PIN NO	21	22	23	24	25	26	27	28	29	30
SYMBOL	B0	B1	B2	B3	B4	B5	B6	B7	GND	CLK
PIN NO	31	32	33	34	35	36	37	38	39	40
SYMBOL	DISP	HSYNC	VSNC	NC	AVDD	AVDD	NC	NC	GND	GND

LED CONNECTOR INTERFACE:

PIN NO	1	2	3	4
SYMBOL	K	NC	NC	A