

ZZE ZP2.5/8**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Product image**

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

Version	Z-series, Strain relief, yellow, 30.1 mm
Order No.	1866230000
Type	ZZE ZP2.5/8
GTIN (EAN)	4032248480838
Qty.	25 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5.62 mm	Depth (inches)	0.2213 inch
Height	75.9 mm	Height (inches)	2.9882 inch
Width	30.1 mm	Width (inches)	1.185 inch
Net weight	3.54 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66 GF 30	Colour	yellow
UL 94 flammability rating	HB		

System specifications

Version	Strain relief
---------	---------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		